


Non-NEMA 30 Amp, 250, 125/250 Volts and 3ØY 120/208 Volts AC 2 Pole, 3 Wire, Grounding and 3 Pole, 3 Wire, Non-Grounding

For Replacement Use Only

IP20
SUITABILITY



Insulgrip® Connector Bodies

Description	Cord Dia.	Catalog Number	
Black and white nylon.	.360"-.930" (9-24)	HBL3333GC	HBL3333C

Note: See pages C-52 and C-53 for accessories.

Single Flush Receptacles

Description	Catalog Number	
Black thermoset, back wired.	HBL3330G	HBL3330

Note: See page C-52 for accessories.


Insulgrip Flanged Receptacles

Description	Catalog Number	
Nylon casing, back wired.	—	HBL3335C

Note: See page C-52 for accessories.

For Replacement Use Only

IP20
SUITABILITY



Insulgrip Connector Bodies

Description	Cord Dia.	Catalog Number	
Black and white nylon.	.350"-1.150" (9-29)	HBL3433GCB	HBL3433C

Note: See pages C-52 and C-53 for accessories.

Single Flush Receptacles

Description	Catalog Number	
Black thermoset, back wired.	HBL3430G	HBL3430

Note: See page C-52 for accessories.

Insulgrip Flanged Receptacles

Description	Catalog Number	
Nylon casing, back wired.	—	—


Note: See page C-52 for accessories.

The devices shown on this page are not listed by Underwriters Laboratories Inc. and are for replacement use only in existing installations.


CAUTION: To avoid electrical shock, review premises carefully and do not use if slot or blade configuration (design) is already in a circuit having a rating differing from the rating of this device.



HBL3333GC




HBL3330G



HBL3335C



HBL3433C



HBL3430

Dimensions in Inches (mm)